NOVITOOL[®] AMIGO[™] Splice Press for Homogeneous Belts

Engineered for Precision Belt Splicing

Splices in homogeneous belting must ensure tight pitch tolerance and be free from pinhole air pockets. With that in mind, everything about the Amigo[™] 625 and 1000 has been designed to do just that. And in typical Novitool[®] tradition, it was made to do it with ease, safety, and speed.

Custom templates are available to secure the belt when cutting and welding the belt ends to ensure accurate pitch control. Preheat mode dries belt ends of moisture to minimize pinholes. The Amigo Splice Press features a transport case for easy storage and transportation, making it ideal for in-shop or on-site splicing.







Patents: www.flexco.com/patents

Accuracy, Speed, and Safety

The Amigo 625 and 1000 feature an integrated blade with a single pass operation that cuts belt edges square. They are designed for operator safety from lacerations as the blade passes through the clamp bars and stores in a blade housing when complete.

The contactless heating element splices the belt in as little as one minute, finishing with a controlled amount of clash. It is also stored within the press when not in use, protecting the operator from possible burns.

The shielded heat zone not only provides consistent heating in various environmental conditions; it also protects the operator from the heat source during splicing. The heater stows and cools inside the press as the belt ends are brought together, fabricating the butt-weld.

Market Applications


- Proteins
- Baking
- Snack
- Fruit and Vegetable





www.flexco.com

Safety Features of the Amigo™ 625 & 1000




Integrated Cutter: Operator is protected from blade during single pass cutting operation.



Cutter Storage Position: Cutter must be in storage position for splicing function to operate.



Shielded Heat Zone: Guard must be closed for heat emitter to function. Operator is protected from heat source during splicing.



Cool Zone: Heater stows and cools inside unit as belt ends are butt-welded together.

NOVITOOL[®] AMIGO[™] Splice Press for Homogeneous Belts

Overview

Features and Benefits:

- Splice time, including the time to heat the press and splice the belt, is **approximately one minute**.
- Pre-heat function dries moisture out of belt ends for **improved splice quality**, free of pinholes where bacteria can grow.
- Unique heating element brings the belt ends to the desired molten state without disrupting the material.
- Exclusive, **built-in safety features** like the integrated belt cutter and shielded heating element eliminates the need for utility knives and protects operators from the heat source.



| Amigo [™] 625 Dimension Information | | | | | | |
|--|---|------------------|--|--|--|--|
| | Dimensions | Weight | | | | |
| Machine | 1000 mm (39.4 in) x 315 mm (12.4 in) x 170 mm (6.7 in) | 24.5 kg (54 lb) | | | | |
| Transport Case (includes additional templates and support equipment) | 1210 mm (47.7 in) x 490 mm (19.3 in) x 385 mm (15.2 in) | 31 kg (68 lb) | | | | |
| Total Weight | | 55.5 kg (122 lb) | | | | |

2

NOVITOOL[®] AMIGO[™] Splice Press for Homogeneous Belts



Custom **Transport Case** *for easy storage and transportation*

| Amigo [™] 1000 Dimension Information | | | | | | |
|--|---|------------------|--|--|--|--|
| | Dimensions | Weight | | | | |
| Machine | 56.1" (1425 mm) × 12.4" (315 mm) × 6.7" (170 mm) | 85 lb (38.5 kg) | | | | |
| Transport Case (includes additional templates and support equipment) | 66.9" (1700 mm) × 19.3" (490 mm) × 15.2" (385 mm) | 80 lb (36.3 kg) | | | | |
| Total Weight | | 165 lb (74.8 kg) | | | | |



NOVITOOL[®] AMIGO[™] Splice Press for Homogeneous Belts

| Amigo™ Press and Cable Ordering Information | | | | | | | | |
|---|------------------------|-----------|---------------------------------|--------------------------------|-----------|--|--|--|
| | Ordering Number | Item Code | | Ordering Number | Item Code | | | |
| Press | | | Cables | | | | | |
| 24.5" (625 mm) | AMIGO-625-SPLICEPRESS | 09726 | 115 volt; single phase; 15 amp | AMIGO-1000-CABLE-1X115-IEC520 | 08585 | | | |
| 42" (1065 mm) | AMIGO-1000-SPLICEPRESS | 08545 | 230 volt; single phase; 7.5 amp | AMIGO-1000-CABLE-1X230-IECL620 | 08586 | | | |

NOTE: Press, cable, and templates are all purchased separately.

| - | o™ 625 Belt Template (| | | | | o™ 1000 Belt Template | | | |
|---|----------------------------|---|-------------------------------------|--|--------------|---------------------------|----------------------------|------------------------------------|--|
| ltem Code | Ordering Number | Belt Manufacturer | Belt Style | Belt Type | ltem Code | Ordering Number | Belt Manufacturer | Belt Style | Belt Type |
| Templa | ates | Ammeraal | | | Templ | ates | Ammeraal | | |
| 09731 AMIG0-625-TMPLT-08592 | Beltech | Center Bar | | | | Beltech | Center Bar | | |
| | AMIGO-625-TMPLT-08592 | Intralox® | ThermoDrive® | 8140 Dual Lug | 08592 | AMIGO-1000-TMPLT-08592 | Intralox [®] | ThermoDrive [®] | 8140 Dual Lu |
| | Volta | SuperDrive™ | FMW & FMB FHW & FHB | | | Volta | SuperDrive™ | FMW & FME FHW & FHB | |
| 09730 | AMIG0-625-TMPLT-08593 | Intralox® | ThermoDrive® | 8050 8026 | 08593 | AMIGO-1000-TMPLT-08593 | Intralox® | ThermoDrive® | 8050 8026 |
| 03730 | AWI00-025-1WI EI-00555 | Mafdel | DEL/DRIVE | DD25 | 08593 | | Mafdel | DEL/DRIVE | DD25 |
| 09732 | AMIG0-625-TMPLT-08594 | Habasit | Cleandrive™ | CD.M50.S-UA.CB CD.M50.S-UA.WB CD.M25.S-UA.CB CD.M25.S-UA.WB | 08594 | AMIG0-1000-TMPLT-08594 | Habasit | Cleandrive™ | CD.M50.S-U CD.M50.S-U CD.M25.S-U CD.M25.S-U |
| 09733 | AMIG0-625-TMPLT-08595 | | | Flat | 08595 | AMIG0-1000-TMPLT-08595 | | | Flat |
| | | Forbo | Fullseal | PD1 U30 & PD2 U34 | | | Forbo | Fullseal | PD1 U30 & P |
| 09734 | AMIG0-625-TMPLT-08596 | Gates® TPU | PosiClean® | PC10 PC20 | 08596 | AMIGO-1000-TMPLT-08596 | Gates® TPU | PosiClean® | PC10 PC20 |
| | | UBR | 1" & 2" Purclean | PS2 & PB3 | | | UBR | 1" & 2" Purclean | PS2 & PB3 |
| | | Beltservice | ProClean Center | PCCDB | | | Beltservice | ProClean Center | PCCDB |
| | | Corporation | Drive Lug | PCCD-MD | | | Corporation | Drive Lug | PCCD-MD |
| | | Daisler® | REOclean® | AT40 | | | Daisler® | REOclean® | AT40 |
| 09735 | AMIG0-625-TMPLT-08597 | Forbo | Fullseal | CD40- U34 | 08597 | AMIG0-1000-TMPLT-08597 | Forbo | Fullseal | CD40- U34 |
| 00700 | | Gates® TPU | CenterClean® | CC40 | 00007 | | Gates® TPU | CenterClean® | CC40 |
| | | UBR | Center Drive Purclean | CD3BLSS | | | UBR | Center Drive PurClean | CD3BLSS |
| | | Yongli Belting | HygienePro™ | U400 | | | Yongli Belting | HygienePro™ | U400 |
| | | Cog-veyor Systems Inc. | Cog-veyor | UBM | 08603 | AMIG0-1000-TMPLT-08603 | Ammeraal | Aeon | Aeon-50 |
| 09736 | AMIG0-625-TMPLT-08710 | | | UWM PBH | 08710 | AMIGO-1000-TMPLT-08710 | Cog-veyor Systems Inc. | | UBM |
| | | | | PWH | | | | Cog-veyor | UWM PBH |
| | | | | PC20 | | | Systems mc. | | PWH |
| 09737 | AMIG0-625-TMPLT-08776 | Gates® TPU | PosiLace™ | CC40 FC12 | 08739 | AMIG0-1000-TMPLT-08739 | Beltservice Corporation | Magnethane™ | PD1 |
| | | UBR | Hinge Lace | | 00733 | | Yongli Belting | HygienePro™ | U300 |
| | AMIGO-625-TMPLT-08788 | Ammeraal Beltech | Full Bar | | 08741 | AMIG0-1000-TMPLT-08741 | ·····g ·····g | | Flat w/Spike |
| | | Beltservice Corporation | ProClean 1" & 2" Pitch Drive Bar | PCPD2B | 08776 | AMIGO-1000-TMPLT-08776 | Gates® TPU Pos | PosiLace™ | PC20 CC40 |
| | | | | PCPD1B-MD | | | | PosiLace | FC12 |
| | | D · 1 @ | | T25 | | AMIG0-1000-TMPLT-08788 | UBR | Hinge Lace | N/A |
| 09738 | | Daisler® | ReoClean® | REO-T50 DB & SB & W | | | Ammeraal Beltech | Full Bar | |
| | | UBR | 1" & 2" Purclean | PS2 & PB3 FMW & FMB | | | Beltservice | ProClean 1" & 2" | PCPD2B |
| | | Volta | DualDrive™ | FHW & FHB | 08788 | | Corporation | Pitch Drive Bar | PCPD1B-MD T25 |
| | | | Mini DualDrive [™] Mini | FMB & FHB FMB & FHB | | | Daisler® | REOclean® | REO-T50 DB |
| | | | SuperDrive™ | | | | UBR | 1" & 2" Purclean | |
| 09739 | AMIGO-625 TMPLT-08847 | Volta | Hinge Splice | M (2.5-5mmH) | | | | DualDrive™ | FMW & FME FHW & FHB |
| Amigo [™] Optional Accesso | | Ordering Number | | Item Code | | | | Mini DualDrive™ | FMB |
| Skiving Tool | | | | 03239 | | | Volta | | FHB |
| - | | RTBS Rough Top Skiver AMIGO-1000-BLADES-5 | | 03239 | | | | Mini | FMB |
| Replacement Blades for Amigo High – Low Temp Friction Tape | | | | | | | | SuperDrive™ | FHB |
| for Flat | | AMIGO-FRICTI | ONTAPE-33X25 | 08604 | 08847 | AMIGO-1000-TMPLT-08847 | Volta | Hinge Splice | M (2.5-5mmH |
| lew Do | oor No. 51 • Anna Salai, N | No. 51 • Anna Salai, Nagalkeni • Pammal Village • | | | 08849 | AMIGO-1000-TMPLT-08849 | Ammeraal Beltech | Soliflex PRO/ Soliflex PRO mini | |
| | | | | | 1 000EE | I ANALCO 1000 TMDIT 000EE | 1 Mafdal | | 10021 |

08855

AMIGO-1000-TMPLT-08855 Mafdel

08856 AMIGO-1000-TMPLT-08856 Mafdel

New Door No. 51 • Anna Salai, Nagalkeni • Pammal Village • Chennai - 600 044 • Tamil Nadu • India Tel: +91-44-4856-6762 • E-mail: info.india@flexco.com

Visit www.flexco.com for other Flexco locations and products.

©2022 Flexible Steel Lacing Company. Novitool® is a registered trademark. Intralox® and ThermoDrive® are registered trademarks of Laitram L.L.C. 05-12-22. For reorder: W1300



POSITIVEBELT

DEL/DRIVE

8140 Dual Lug FMW & FMB

CD.M25.S-UA.WB

PD1 U30 & PD2 U34

DD25 CD.M50.S-UA.CB CD.M50.S-UA.WB CD.M25.S-UA.CB

U300 Flat w/Spikes PC20

M (2.5-5mmH)

P02-L

DD50

REO-T50 DB & SB & W